



Locking C clamp



Order data

Order number	862100
GTIN	4008158009636
Item class	83K

Description

Version:

Quenched and tempered profile steel beam; **quick adjustment; steplessly adjustable clamp jaw; clamping force adjustable** (maximum 4000 N).

With C-shaped yoke arms for clamping profiled material with high flanges.

Throat: 80 mm

Technical description

Jaw capacity	110 mm
Throat	80 mm
Type of product	Grip wrench