



Welder's angle clamp, maximum clamping range: 120mm



Order data

Order number	862500 120
GTIN	4008158016825
Item class	83K

Description

Version:

Malleable cast iron base body with strong cleanly machined support faces (clamping angle 90°). Clamping jaws movable for **different material cross-sections**.

Application:

For clamping components at the correct angle during welding and/or assembly work.

Technical description

maximum clamping range	120 mm
maximum aperture	100 mm
Weight	7.8 kg
Jaw height	61 mm
Type of product	Welder's angle clamps

