

**Claw beam clamp, Jaw capacity: 300mm****Order data**

Order number	861600 300
GTIN	4008158035819
Item class	83K

Description**Version:**

Fixed beam of bright drawn steel (special profile), electro-galvanised. Sliding jaw of steel with trapezoidal thread spindle and jaw anvil that can tilt up to 30°. The clamp can be used for **spreading tasks** (exerting outwards pressure) by reversing the sliding jaw.

Application:

Maximum clamping pressure up to approx. 7500 N.

Technical description

Cross section of the slide rail	28×11 mm
Jaw capacity	300 mm
Weight	2.4 kg
Throat	120 mm
Type of product	Clamp

Accessories

Pressure piece

861605