



## Cutting disc SGP STEEL EXTRA THIN, Disc Ø: 115mm



### Order data

Order number	563440 115
GTIN	4007220103890
Item class	55T

### Description

#### Version:

Extra thin **high performance cutting disc** for very quick low-burr cutting with low thermal stress and easy ergonomic cut guidance. Very tough, very high cutting performance and outstanding service life.

#### Specification:

**A60Q-CERAMIC SGP STEEL.**

### Technical description

Shape description	flat
Disc Ø	115 mm
Disc thickness	1 mm
Bore Ø	22.23 mm
for material thicknesses	3 - 5 mm
Grinding medium code	Ceramic
recommended approach angle	90 degrees

optimised for material	HSS
Propulsive equipment	Angle grinders
maximum circumferential speed	80 m/s
Type of product	Cutting disc

## User data

	Suitability	$V_c$	ISO code
Steel < 900 N/mm <sup>2</sup>	suitable		
Steel < 1400 N/mm <sup>2</sup>	suitable		
Steel < 55 HRC	suitable		
Steel < 60 HRC	suitable		
Steel < 67 HRC	suitable		
GG(G)	suitable only under restricted conditions		
dry	suitable		