



Universal clamp (clamping hand), Type: 50



Order data

| | |
|--------------|---------------|
| Order number | 861900 50 |
| GTIN | 4045197167521 |
| Item class | 82C |

Description

Version:

With trapezoidal thread spindle and 2 swing clamping jaws. Each clamping jaw has 3 smooth faces and a cross-Vee face; can be used for **clamping the most diverse components**.

Application:

For **internal** and **external clamping** of the most diverse workpiece shapes.

Material:

Spindle and clamping block of burnished steel.

Technical description

| | |
|---------------------------|------------|
| Capacity in compression a | 0 - 50 mm |
| maximum clamping force | 2000 N |
| Clamping depth c | 30 mm |
| Capacity in tension b | 32 - 82 mm |
| Type of product | Clamp |