

**Claw beam clamp, Jaw capacity: 1000mm****Order data**

Order number	861600 1000
GTIN	4008158035833
Item class	83K

**Description****Version:**

Fixed beam of bright drawn steel (special profile), electro-galvanised. Sliding jaw of steel with trapezoidal thread spindle and jaw anvil that can tilt up to 30°. The clamp can be used for **spreading tasks** (exerting outwards pressure) by reversing the sliding jaw.

**Application:**

**Maximum clamping pressure up to approx. 7500 N.**

**Technical description**

Weight	3.8 kg
Throat	120 mm
Jaw capacity	1000 mm
Cross section of the slide rail	28×11 mm
Type of product	Clamp

---

## Accessories

Pressure piece

861605