



Heavy all-steel high-performance clamp with special jaw anvil, Jaw capacity: 500mm



Order data

Order number	861310 500
GTIN	4008158007625
Item class	83K

Description

Version:

Beam and fixed jaw made of bright steel section (special profile), tempered and electro-galvanised. Slide jaw made of steel, drop-forged, tempered, and electro-galvanised. Wear-resistant smooth-running steel spindle with trapezoidal thread. Long working life due to heat-resistant special pressure pad with sintered steel inlay. Spindle tempered and burnished with adjustable clamp handle.

Can tilt through 35°.

Application:

For heaviest duty clamping of workpieces in steel construction, blacksmith's shops, HGV bodywork, machine tool manufacture etc. The movable special jaw anvil permits clamping diagonal workpieces up. **Maximum clamping pressure up to approx. 22000 N.**

Technical description

Throat	175 mm
Cross section of the slide rail	40×20 mm

Jaw capacity	500 mm
Weight	6.7 kg
Type of product	Clamp

Accessories

Spindle with tightening bar and pressure plate	861340
Pressure plate including fastenings	861130