



## Universal clamp (clamping hand), Type: 100



### Order data

Order number	861900 100
GTIN	4045197167545
Item class	82C

### Description

#### Version:

With trapezoidal thread spindle and 2 swing clamping jaws. Each clamping jaw has 3 smooth faces and a cross-Vee face; can be used for **clamping the most diverse components**.

#### Application:

For **internal** and **external clamping** of the most diverse workpiece shapes.

#### Material:

Spindle and clamping block of burnished steel.

### Technical description

Capacity in compression a	0 - 100 mm
Clamping depth c	60 mm
Capacity in tension b	50 - 150 mm
maximum clamping force	3000 N
Type of product	Clamp