

Garant
Four-way ratchet ring spanner "4 in 1", Type: 10-19

Order data

Order number	614847 10-19
GTIN	4045197967794
Item class	61B

Description
Version:

With particularly free-running sturdy ratchet at each end – reversible for left and right hand tightening. The 2 ends have different widths across flats. Extremely small working arc of 5°.

Material:

Chrome vanadium steel, matt chrome-plated.

Technical description

maximum ring \varnothing D2	35 mm
Width across flats 4	19 mm
Width across flats 3	17 mm
Width across flats 2	13 mm
Width across flats	metric
maximum ring height h_1	15 mm
maximum ring height h_2	20 mm
maximum ring \varnothing D1	26 mm
Width across flats 1	10 mm
overall length L	210 mm
No. of teeth	72
Working arc	5 degrees

Material	Chrome vanadium steel
Surface	matt chrome-plated
Ratchet reversible	yes
Type of product	Spanner