

**Garant**
**Four-way ratchet ring spanner "4 in 1", Type: 8-13**

**Order data**

Order number	614847 8-13
GTIN	4045197967787
Item class	61B

**Description**
**Version:**

With particularly free-running sturdy ratchet at each end – reversible for left and right hand tightening. The 2 ends have different widths across flats. Extremely small working arc of 5°.

**Material:**

Chrome vanadium steel, matt chrome-plated.

**Technical description**

maximum ring $\varnothing$ D1	20.2 mm
Width across flats	metric
Width across flats 2	10 mm
maximum ring height $h_2$	16.8 mm
maximum ring $\varnothing$ D2	24.8 mm
overall length L	150 mm
Width across flats 4	13 mm
Width across flats 3	12 mm
maximum ring height $h_1$	13.8 mm
Width across flats 1	8 mm
No. of teeth	72
Working arc	5 degrees

Material	Chrome vanadium steel
Surface	matt chrome-plated
Ratchet reversible	yes
Type of product	Spanner