

**Cordless wet / dry vacuum cleaner, Type: M18VC2-0****Order data**

Order number	070230 M18VC2-0
GTIN	4058546219741
Item class	03L

Description**Version:**

Portable and powerful 18 V cordless wet / dry vacuum cleaner.

- **80 mbar vacuum.**
- **Running time up to 30 minutes on one battery charge (9.0 Ah).**
- **Integral blow-out function.**
- **HEPA filter traps 99.97 % of all dust particles.**
- **Tank volume solid / liquid: 9.8 / 7.5 l.**
- **Air flow 1300 l/min**

Supplied with:

Without battery and without charger.

Supplied with filter, suction hose, coarse dirt nozzle and crevice nozzle.

Note:

See No. 073816, No. 073827 and No. 073840 for suitable replacement batteries and chargers.

Technical description

Container volume	7.5 l
Manufacturer's designation	M18VC2-0
Volumetric flow	1300 l/min

Battery voltage	18 V
Length of suction hose	0.47 m
Number of rechargeable batteries contained	0
Type of rechargeable battery	Lithium-ion
Weight without battery	5.3 kg
Power supply	Rechargeable battery-powered
suitable battery - supplier / battery type / voltage	Milwaukee type B 18 V
Type of product	Wet and dry vacuum cleaners

Accessories

Battery charger Type M1218SC	073840 M1218SC
Battery charger Type M1418C6	073840 M1418C6