



## Welder's angle clamp, maximum clamping range: 90mm



### Order data

Order number	862500 90
GTIN	4008158016832
Item class	83K

### Description

**Version:**

Malleable cast iron base body with strong cleanly machined support faces (clamping angle 90°). Clamping jaws movable for **different material cross-sections**.

**Application:**

For clamping components at the correct angle during welding and/or assembly work.

### Technical description

maximum aperture	60 mm
Weight	3.8 kg
maximum clamping range	90 mm
Jaw height	35 mm
Type of product	Welder's angle clamps

