

**LED cordless lamp 0 version without battery, 18 V, Type: GLI18300****Order data**

Order number	073205 GLI18300
GTIN	3165140876193
Item class	03B

**Description****Version:**

Robust 18 V Li-ion cordless lamp with adjustable LED head. 6 powerful LEDs with 300 Lumens and very long working life.

Flexible applications thanks to the adjustable lighting head positions.

**Supplied with:**

**Cordless lamp without battery and without charger.**

**Note:**

Suitable spare batteries and chargers can be found under No. 073851– 073866.

**Technical description**

Battery voltage	18 V
Manufacturer's designation	GLI 18V-300
Number of rechargeable batteries contained	0
Type of rechargeable battery	Lithium-ion
Weight without battery	300 g

Illumination	300 lm
Bulb	LED module
Power supply	Rechargeable battery-powered
ATEX zone	no
Product name attribute	18 V
suitable battery - supplier / battery type / voltage	Bosch 18 V
Type of product	Work lamp

---

## Accessories

Li-ion battery Battery type, battery voltage B18 V	073853 B18
Li-ion battery Battery type, battery voltage B18 V	073851 B18
Battery charger Type 1880CV	073866 1880CV