



LED cordless lamp 0 version without battery, 18.0 V, Type: M18ONESLSP



Order data

Order number	073211 M18ONESLSP
GTIN	
Item class	07A

Description

Version:

Robust Li-Ion battery lights with high light intensity.

- **ONE-KEY™ technology for extended settings and wireless control of the floodlight from distances up to 15 m.**
- **Optimised brightness and running time, specifying the power between 0 and 4400 Lumen.**
- **Programming automatic time switching (the floodlight switches itself on and off automatically at specific times).**
- **180° and 360° electronic light control for floodlighting or area lighting.**
- **Hybrid: For use with M18™ REDLITHIUM-ION™ batteries or mains cable.**

The floodlight offers complete 360-degree illumination and is an ideal solution for floodlighting including overhead working.

- **TRUEVIEW™ highly efficient lighting solution.**
- **Reinforced suspension hole and self-centring metal hook for suspending the floodlight from pins or pipes.**
- **If used with a mains cable, multiple floodlights can be chained together in series.**

Function:

IP54: Protected against splashed water from all directions and protected against penetration of dust into the inside (protected against dust), also completely protected against touching.

Suitable for:

Milwaukee 18 V batteries (No. 073816 MB18 and 073827 MB18).

Supplied with:
Cordless lamp without battery and without charger.

Technical description

Battery voltage	18 V
Manufacturer's designation	M18ONESLSP-0
Spread angle	180 - 360 degrees
IP Index of Protection	IP 54
Illumination step 2	2100 lm
Illumination time	8 h
Number of rechargeable batteries contained	0
Type of rechargeable battery	Lithium-ion
Weight without battery	4700 g
Bulb	LED module
Illumination	4400 lm
Power supply	Rechargeable battery-powered
ATEX zone	no
Product name attribute	18.0 V
suitable battery - supplier / battery type / voltage	Milwaukee type B 18 V
Type of product	Work lamp

Accessories

Li-ion system M18B5 Battery type MB18	073816 MB18
Battery charger Type M1218FC	073840 M1218FC
Battery charger Type M1218C	073840 M1218C