



## Cordless impact wrench / impact driver, Type: GDR18160



### Order data

Order number	074052 GDR18160
GTIN	3165140889117
Item class	03B

### Description

#### Version:

Cordless impact wrench / impact driver

- **Reversible.**
  - **Battery charge display.**
- Compact 18 V / 2.0 Ah cordless impact wrench.
- **High torque and high impact rate (3,200 impacts/minute) for rapid progression of work when tightening screws in metal (up to M14) and wood.**
  - **Very short body for perfect handling even in confined spaces and overhead.**

#### Advantage:

Powerful thanks to high torque.

#### Supplied with:

Supplied with 2x Li-ion batteries, charger, L-BOXX

#### Note:

Suitable replacement batteries and chargers can be found under No. 073851 – 073867.

Packaging: Modular case (L-Boxx)

suitable battery - supplier / battery type / voltage: Bosch 18 V

Manufacturer's designation: GDR V18-160

Number of rechargeable batteries contained: 2

Type of rechargeable battery: Lithium-ion

Battery capacity: 2 A·h

Battery voltage: 18 V  
 maximum screw Ø (8.8 - 12.9): M14

### Technical description

Tool arbor size	1/4 in
typical application	Strong
suitable battery - supplier / battery type / voltage	Bosch 18 V
Packaging	Modular case (L-Boxx)
Weight	1.7 kg
maximum vibration to EN	10 m/s <sup>2</sup>
maximum screw Ø (8.8 - 12.9)	M14
Height	234 mm
Battery capacity	2 A·h
Manufacturer's designation	GDR V18-160
maximum speed 1st speed	2800 min <sup>-1</sup>
Length	153 mm
Tool arbor drive profile	Internal hexagon drive
Battery voltage	18 V
Number of impacts	0 - 3200 min <sup>-1</sup>
maximum torque hard	160 N·m
Number of rechargeable batteries contained	2
Type of rechargeable battery	Lithium-ion
Power supply	Rechargeable battery-powered
Suitable for material	wood
Type of product	Impact wrench

### Accessories

Battery charger Type 1880CV	073866 1880CV
-----------------------------	---------------

Li-ion battery Battery type, battery voltage B18 V

073851 B18