



Cordless core drilling machine, Type: 71700161

Order data

Order number	076524 71700161
GTIN	4014586888163
Item class	03F

Description

Version:

- **For the best performance we recommend the FEIN HighPower battery with 5.2 Ah.**
- **Reversible.**
- **Extra narrow pre-magnetised permanent magnet.**

Small single-speed magnetic core drilling machine with powerful lift and brushless EC motor. Very high functionality for mobiles work around the building site.

- **Convenient magnetic clamping force display.**
- **Tilt sensor.**
- **Electronic speed setting.**
- **"Memory Function" speed memory.**

Standard:

Small single-speed magnetic core drilling machine with powerful lift and brushless EC motor. Very high functionality for mobile work around the building site.

- **FEIN HighPower Li-ion battery.**
- **Convenient magnetic clamping force display.**
- **Tilt sensor.**
- **Reversible.**

Supplied with:

AKBU 35 PMQ Select **without battery, incl.** coolant pump, lashing strap, swarf hook, centring pin, guard, drive-out drift, carrying case.

Note:

A suitable battery can be optionally obtained under No. 073834 FE 18.

Packaging: Carrying case

suitable battery - supplier / battery type / voltage: Fein type E 18 V

Manufacturer's designation: AKBU 35 PMQ

Battery voltage: 18 V

Battery capacity: 52 A·h

maximum speed: 130 - 520 rpm

Tool arbor shape: QuickIN / MT2

maximum machine tap Ø in steel: M14

Technical description

Type of product
