



## Stepped jaws movable, for type: 200



### Order data

Order number	361450 200
GTIN	4250364403399
Item class	34A

### Description

**Version:**

Movable jaw.

Sizes 90, 125, and 160 with **Click quick-change system**, for No. 361440 only in sizes 90 and 125.

**Application:**

For clamping parallel pre-machined components. Tapped holes M10 and M6 for taking front jaws with click quick-change system for click inserts and jaws.

Accepts parallel inserts on high side or stepped side (No. 361950; 361960; 361970).

**Material:**

Hardened steel, ground surfaces.

**Suitable for:**

All types TC, LC, Garant-NC, Titan and the earlier NC version.

**Supplied with:**

Fastening screws. 1 stepped jaw.

### Technical description

Length $l_1$	65 mm
Height $h_1$	25 mm
Jaw length $l$	115 mm

Jaw height h	60 mm
Jaw width b	200.4 mm
suitable for colour code	TC
suitable for colour code	LC
suitable for colour code	NC8
Type of product	Vice jaws