

Ansell**Pair of gloves HyFlex® 11-816, Glove size: 7****Order data**

Order number	094356 7
GTIN	10076490449992
Item class	04P

Description**Version:**

HyFlex® 11-816. Extremely thin and robust gloves of **18-gauge** knitted fabric. **Increased working life and resistance to abrasion** thanks to the foam coating with FORTIX™ Abrasion Resistance Technology. **Free of solvents and toxins**, certified to the Oeko-Tex standard. Particularly suitable for light assembly work with high demands on precision, final assembly of electric motors, air conditioning systems, wiring harnesses.

Standard:

EN 388; EN ISO 21420

Note:

The minimum order quantity corresponds to one pack unit quantity (VPE) or a multiple thereof.

Technical description

Series	HyFlex®
Glove size	7
Protection category	Category II
Type of glove	Multi-purpose gloves

Clothing standard	Oeko-Tex Standard 100
Contents	12
Glove characteristics	DMF-free
Glove characteristics	Suitable for allergy sufferers
Glove characteristics	free of latex
Glove characteristics	Silicone-free
EN 388	4121A
Backing material	Nylon Spandex
Coating	Nitrile foam
Coating variant	The palms of the hands
Application range	Precision
Length	219 mm
Colour	black / blue
Weight	20,4 g
Knitted technology	18G
Application	reusable
Material	Nitrile foam
Cut protection class	A
Type of product	Multi-purpose gloves