



Cordless impact wrench / impact driver, Type: M18ONEFF12



Order data

Order number	074010 M18ONEFF12
GTIN	4058546028992
Item class	03L

Description

Version:

Robust and **powerful FUEL™ cordless impact wrench** with **brushless POWERSTATE™ EC motor**, for long motor service life and high energy efficiency. Sturdy **metal gearbox casing** and ergonomic **central handle with soft-grip coating**. Stage of charge display, LED illumination of the working area. Reversible, with electronic speed control. **REDLINK PLUS™ electronics** – for unique power management:

- **With system communication between the drive machine and battery.**
 - **With overload protection for longer working life of the battery, motor, and gearbox.**
- DRIVE CONTROL™ permits quick switching between the 4 available settings with different speeds and torques.
- **Compact design.**
 - **Stage 4 for an optimum mix of power and precision when undoing screws.**
 - **Powerful 1356 Nm torque.**
 - **1/2 inch snap ring socket.**
 - **ONE KEY™ app for individualising the tool settings.**
 - **ONE KEY™ tool tracker & security permits amongst other things a display of the latest position of the device.**

Version of the advertising text:

Robust and **powerful FUEL™ cordless impact screwdriver** with **brushless POWERSTATE™ EC motor** for long motor service life and high energy efficiency.

- **Compact design.**
- **Stage 4 for an optimum mix of power and precision when undoing screws.**

Advantage:

DRIVE CONTROL™.

Supplied with:

Supplied with 2× Li-ion batteries, charger, HD box, belt clip.

Note:

For matching spare batteries and accessories see from No. 073808.

Technical description

Number of impacts 4th setting	0 - 2100 min ⁻¹
suitable battery - supplier / battery type / voltage	Milwaukee type B 18 V
Number of impacts 1st stage	0 - 950 min ⁻¹
Battery voltage	18 V
Packaging	Modular case (HD=Heavy Duty)
maximum torque 2nd step	400 Nm
typical application	Heavy Duty
maximum torque 3rd step	1356 Nm
maximum torque 4th setting	1356 Nm
Weight	3.3 kg
Number of impacts 3rd stage	0 - 2100 min ⁻¹
Battery capacity	5 Ah
Tool arbor drive profile	External square drive
maximum torque 1st step	130 Nm
Number of impacts 2nd stage	0 - 1750 min ⁻¹
maximum screw Ø (8.8 - 12.9)	M33
Manufacturer's designation	M18ONEFHIWF12-502X
Tool arbor size	1/2 in
App link	OneKey
Number of rechargeable batteries contained	2

Type of rechargeable battery	Lithium-ion
Power supply	Rechargeable battery-powered
Suitable for material	Steel
Type of product	Impact wrench

Accessories

Battery charger Type M1218FC	073840 M1218FC
Battery charger Type M1218C	073840 M1218C
Li-ion system M18B5 Battery type MB18	073816 MB18