



Cordless impact wrench / impact driver, Type: M18ONEFF34



Order data

Order number	074010 M18ONEFF34
GTIN	4058546029029
Item class	03L

Description

Version:

Robust and **powerful FUEL™ cordless impact wrench** with **brushless POWERSTATE™ EC motor**, for long motor service life and high energy efficiency. Sturdy **metal gearbox casing** and ergonomic **central handle with soft-grip coating**. Stage of charge display, LED illumination of the working area. Reversible, with electronic speed control. **REDLINK PLUS™ electronics** – for unique power management:

- **With system communication between the drive machine and battery.**
 - **With overload protection for longer working life of the battery, motor, and gearbox.**
- DRIVE CONTROL™ permits quick switching between the 4 available settings with different speeds and torques. Cordless impact wrench / impact driver with snap ring provides up to 1627 Nm of tightening torque and replaces wired and pneumatic devices. DRIVE CONTROL enables quick switching between the 4 available settings with different speeds and torques.
- **Compact design.**
 - **Stage 4 for an optimum mix of power and precision when undoing screws.**
 - **Powerful 1627 Nm torque.**
 - **3/4 inch snap ring socket.**
 - **ONE KEY™ app for individualising the tool settings.**
 - **ONE KEY™ tool tracker & security permits amongst other things a display of the latest position of the device.**

Version of the advertising text:

Robust and **powerful FUEL™ cordless impact screwdriver** with **brushless POWERSTATE™ EC motor** for long motor service life and high energy efficiency.

Advantage:

DRIVE CONTROL™.

Supplied with:

Supplied with 2× Li-ion batteries, charger, HD box, belt clip.

Note:

For matching spare batteries and accessories see from No. 073808.

Technical description

Battery capacity	5 Ah
suitable battery - supplier / battery type / voltage	Milwaukee type B 18 V
Number of impacts 2nd stage	0 - 1850 min ⁻¹
Packaging	Modular case (HD=Heavy Duty)
maximum torque 3rd step	1627 Nm
maximum torque 4th setting	1627 Nm
Tool arbor drive profile	External square drive
maximum torque 1st step	250 Nm
maximum screw Ø (8.8 - 12.9)	M33
Manufacturer's designation	M18ONEFHIWF34-502X
typical application	Heavy Duty
Weight	3.2 kg
Number of impacts 3rd stage	0 - 2400 min ⁻¹
Number of impacts 4th setting	0 - 2400 min ⁻¹
Battery voltage	18 V
Number of impacts 1st stage	0 - 850 min ⁻¹
maximum torque 2nd step	500 Nm
Tool arbor size	3/4 in
App link	OneKey
Number of rechargeable batteries contained	2
Type of rechargeable battery	Lithium-ion

Power supply	Rechargeable battery-powered
Suitable for material	Steel
Type of product	Impact wrench

Accessories

Battery charger Type M1218C	073840 M1218C
Li-ion system M18B5 Battery type MB18	073816 MB18
Battery charger Type M1218FC	073840 M1218FC