



## Pair of gloves HyFlex® 11-541, Glove size: 7



### Order data

Order number	094563 7
GTIN	10076490458581
Item class	04P

### Description

#### Version:

HyFlex® 11-541. Very light-weight gloves with 18 gauge knitting technology and also high cut resistance (class D to EN 388:2016) due to the combined use of INTERCEPT™ and KEVLAR® yarn. Thin and yet robust nitrile foam coating. Ideal for assembling sharp-edged metal parts.

#### Standard:

EN 388; EN 420

#### Note:

The minimum order quantity corresponds to one pack unit quantity (VPE) or a multiple thereof.

Cut protection class: D

Colour: black / grey

silicone-free: yes

### Technical description

Glove size	7
silicone-free	yes
Type of glove	Cut-resistant gloves

Protection category	Category II
Contents	12
Glove characteristics	Silicone-free
Glove characteristics	Suitable for touch screens
Glove characteristics	free of latex
Knitted technology	18G
Washing	40 °C coloureds
EN 388:2016	4X21D
EN 407	X1XXXX
Backing material	INTERCEPT™, Kevlar
Coating	Nitrile foam
Material	Nitrile foam
Coating variant	The palms of the hands
Application range	All-round
Colour	black / grey
Weight	24 g
Length	196 mm
Application	reusable
Cut protection class	D
Type of product	Cut-resistant gloves