

Ansell**Pair of gloves HyFlex® 11-542, Glove size: 8****Order data**

Order number	094568 8
GTIN	10076490449565
Item class	04P

Description**Version:**

HyFlex® 11-542. Glove with Class F ultra-high cut protection. Special lightweight design for good wearing comfort and good freedom of movement for the fingers. The back of the hand is breathable and the dirt-resistant nitrile coating permits handling of hot objects up to 100 °C for short periods of time.

Standard:

EN 388; EN ISO 21420

Note:

The minimum order quantity corresponds to one pack unit quantity (VPE) or a multiple thereof.

Technical description

silicone-free	yes
Glove size	8
Protection category	Category II
Type of glove	Cut-resistant gloves
Contents	12

Glove characteristics	Silicone-free
Glove characteristics	Suitable for touch screens
Glove characteristics	free of latex
Knitted technology	13G
EN 388	4X32F
EN 407	X1XXXX
Backing material	INTERCEPT™
Coating	Nitrile
Material	Nitrile
Coating variant	The palms of the hands
Application range	All-round
Colour	black
Standard	EN 407
Weight	30.9 g
Contact heat up to	100 °C
Length	213 mm
Application	reusable
Cut protection class	F
Type of product	Cut-resistant gloves