

uvex**Pair of gloves uvex phynomic C5, Glove size: 9**

Order data

Order number	094548 9
GTIN	4048612051719
Item class	04U

Description

Version:

uvex phynomic C5. Light-weight cut-resistant gloves with good touch sensitivity, with moisture-resistant and flexible water-based polymer coating. Very good grip in dry and slightly moist working environment. Suitable for use by those with sensitive skin (dermatologically confirmed). **uvex phynomic series.** Especially lightweight cut-resistant gloves, with a good fit. Ideal for activities for which high touch sensitivity is required. To Öko-Tex® standard 100 and free of silicone.

Standard:

EN 388; EN 420

Note:

The minimum order quantity corresponds to one pack unit quantity (VPE) or a multiple thereof.

Cut protection class: C

Colour: grey/blue

Technical description

Glove size	9
Protection category	Category II

Type of glove	Cut-resistant gloves
Glove characteristics	Silicone-free
Glove characteristics	Levnedsmiddelcertificering
Clothing standard	Oeko-Tex Standard 100
EN 388:2016	4X42C
Backing material	Polyamide, HPPE
Coating	Nitrile
Application range	Precision
Colour	grey/blue
Cut protection class	C
Type of product	Cut-resistant gloves