

## Ansell

### Pair of gloves ActivArmr Hycron® 27-607, Glove size: 9



#### Order data

Order number	094430 9
GTIN	10076490102507
Item class	04P

#### Description

##### Version:

ActivArmr Hycron® series. **Hard-wearing gloves** of jersey cotton with nitrile coating for the most demanding applications. High resistance to sharp-edged and chafing materials. Robust and more flexible than PVC, three times longer service life than heavy leather gloves. **Effective barrier against greases and oils.** Particularly suitable for rough castings, moulded plastic parts, steel bar, sheet metal, high-tensile cable, building materials, unfinished wood. With knitted cuffs and 3/4 coating for maintaining better breathability.

##### Standard:

EN 388; EN ISO 21420

Antistatisch gemäß EN 1149.

##### Note:

The minimum order quantity corresponds to one pack unit quantity (VPE) or a multiple thereof.

#### Technical description

Accuracy of fit	good
DMF-free	no
silicone-free	yes

Material of coating	Nitrile
Oil grip	good
Glove size	9
Touch sensitivity	medium
Breathability	medium
Wet grip	good
Heat protection	not available
Series	Hycron®
Protection category	Category II
Type of glove	Multi-purpose gloves
Contents	12
Glove characteristics	Silicone-free
Glove characteristics	free of latex
EN 388	4221X
Backing material	Cotton
Coating	Nitril
Coating variant	3/4 coating
Application range	Heavy Duty
Length	246 mm
Colour	blue
Weight	57 g
Application	reusable
Material	Nitrile
Type of product	Multi-purpose gloves