

3M**Velour-backed abrasive disc (CER) Hookit 775L Multiple holes, Ø 150 mm, Grit: 320****Order data**

Order number	567792 320
GTIN	50076308470826
Item class	53M

Description**Version:**

With **stable film backing**. Dust-repellent coating prevents premature clogging.

Advantage:

- **More uniform surface finish due to outstanding grit support.**
- **Improved tear resistance when the edges are stressed.**

Application:

Can be used wet or dry on wood, paint, metal and plastic surfaces.

Cubitron™ II precision grit with the advantage of **quicker material removal** and more **consistent surface finish on large areas** (sheet metal work).

Technical description

Series	775L
Grinding media	Cubitron™ II
Grinding medium code	Ceramic
Iron, sulphur and chlorine constituents	< 0.1 %

Product name attribute	Ø 150 mm
Propulsive equipment	Orbital sander
maximum circumferential speed	40 m/s
Type of product	Velour-backed abrasive disc

User data

	Suitability	V _c	ISO code
Alu Mg	suitable		
Steel < 900 N/mm ²	suitable		
Steel < 1400 N/mm ²	suitable		
Steel < 55 HRC	suitable		
Steel < 60 HRC	suitable		
Steel < 67 HRC	suitable only under restricted conditions		
INOX	suitable only under restricted conditions		
Ti	suitable only under restricted conditions		
CuZn	suitable		
Plastic, GRP	suitable		
Wood	suitable		
Paint	suitable		
Uni	suitable		
wet maximum	suitable		
dry	suitable		