

Edge finder TN, Contact point Ø: 10/4mm



Order data

Order number	359005 10/4
GTIN	4260192272951
Item class	38D

Description

Version:

The contact point has a flexible connection to the body via a spring, with an **alignment accuracy of 0.01 mm.**

All parts fully hardened and ground.

Non-magnetic. With stepped contact point 10 and 4 mm Ø.

Application:

For alignment of component reference surfaces or edges.

Spindle speed approx. 600 rpm.

Technical description

Tool shank Ø	10 mm
Contact point Ø	10 mm
Overall length	90 mm
Type of product	Probes

