

**Optical zero setter, Type: 60****Order data**

Order number	359081 60
GTIN	4045197973528
Item class	32B

Description**Version:**

Special hardened steel.

Function:

- **Approach the contact face with the tool upright. When the LED lights up, the reference dimension 60 mm (± 0.01) has been reached. A safety spring range of approx. 2 mm is provided for overdrive.**
- **Size 60M is magnetic for horizontal use.**

Application:

For zeroing tools and for determining the machine spindle reference point.

Supplied with:

With test certificate and instruction manual.

Special battery No. 081560 size 357.

Note:

For use only on electrically conductive workpieces. Not waterproof.

Technical description

Foot width b	31 mm
--------------	-------

Head width c	18 mm
Version	Standard
Number of batteries contained	1
Article no of the battery / rechargeable battery fitted	081560 357
Height a	60 mm
Type of product	Zeroing device

Accessories

Button cell / special battery Battery type 357	081560 357
--	------------