



## Cordless grease gun 562 bar, Type: M18GG



### Order data

Order number	083568 M18GG
GTIN	4002395000340
Item class	03L

### Description

**Version:**

For filling with loose grease (contents up to 500 ml) or with cartridges (contents 400 g). **Suitable for greases up to NLGI 3.**

With bleed valve. Grease gun length 355 mm, hose length 1219 mm.

**Supplied with:**

Charger, hose with angle coupling, carrying case.

**Note:**

For matching spare batteries and accessories see from No. 073814.

### Technical description

Hose connection thread	1/8 inch
Battery voltage	18 V
suitable cartridge	083590
Manufacturer's designation	M18GG
suitable for cartridge size	400 g
Filling volume loose material	500 cm <sup>3</sup>
Battery capacity	2 Ah

Number of rechargeable batteries contained	1
Type of rechargeable battery	Lithium-ion
Power supply	Rechargeable battery-powered
Packaging	Carrying case
suitable battery - supplier / battery type / voltage	Milwaukee type B 18 V
Type of product	Grease gun

## Accessories

Li-ion system M18B2 Battery type MB18	073827 MB18
Multi-purpose grease cartridge forStandard grease guns Type UNI	083590 UNI
Multi-purpose grease cartridge forStandard grease guns Type PLUS	083590 PLUS