



External micrometer, Measuring range: 0-25mm



Order data

Order number	420542 0-25
GTIN	4250099600209
Item class	46P

Description

Version:

Precision lapped, carbide-tipped measuring faces. Hardened and ground measuring spindle. Higher accuracy than DIN 863. Locking by clamping screw. With sensitive ratchet and hand temperature protection. Clearly engraved black divisions and numerals.

Application:

Particularly suitable for inspection work due to the direct 5 µm reading.

Technical description

Scale divisions	0.005 mm
Calibration	B1
Micrometer barrel graduations	1/50 mm
Error limit	1.5 µm
Barrel Ø	25 mm
Measuring range	0 - 25 mm
Type of spindle	hardened and ground
Spindle Ø	8 mm
Standard	Manufacturer's standard
Ratchet	yes

Hand temperature protection	yes
Measurement technology	analogue
Packaging	sturdy box
Type of product	External tube micrometer

Services

DAkkS calibration External micrometer without setting dimension maximum measuring range 100 mm	022010 100
Calibration External micrometer without setting dimension maximum measuring range 25 mm	022000 25