

**External micrometer, Measuring range: 50-75mm****Order data**

Order number	420542 50-75
GTIN	4250099600223
Item class	46P

Description**Version:**

Precision lapped, carbide-tipped measuring faces. Hardened and ground measuring spindle. Higher accuracy than DIN 863. Locking by clamping screw. With sensitive ratchet and hand temperature protection. Clearly engraved black divisions and numerals.

Application:

Particularly suitable for inspection work due to the direct 5 µm reading.

Technical description

Barrel Ø	25 mm
Calibration	B1
Type of spindle	hardened and ground
Spindle Ø	8 mm
Scale divisions	0.005 mm
Measuring range	50 - 75 mm
Error limit	2 µm
Micrometer barrel graduations	1/50 mm
Standard	Manufacturer's standard
Ratchet	yes

Hand temperature protection	yes
Measurement technology	analogue
Packaging	sturdy box
Type of product	External tube micrometer

Services

DAkkS calibrationExternal micrometer without setting dimension maximum measuring range 100 mm	022010 100
CalibrationExternal micrometer without setting dimension maximum measuring range 100 mm	022000 100