

ejendals

Pair of cold protection gloves Tegera® 117, Glove size: 7



Order data

Order number	094821 7
GTIN	7392626010611
Item class	04R

Description

Version:

Tegera® 117. **Comfortable cold protection gloves** of full-grain goatskin and nylon. Robust thanks to **reinforcing elements** on the fingers and thumbs. Suitable for precision work, due to the **outstanding finger tip sensitivity**. With hook and loop fastening.

Version of the advertising text:

Tegera® 117. **Comfortable cold protection gloves** of full-grain goatskin and nylon. Robust thanks to **reinforcing elements** on the fingers and thumbs. Suitable for precision work, due to the **outstanding finger tip sensitivity**. With hook and loop fastening.

Application:

For windy, cold or wet working conditions.

Use of the advertising text:

For windy, cold or wet working conditions.

Standard:

EN 388; EN 511

Note:

The minimum order quantity corresponds to one pack unit quantity (VPE) or a multiple thereof.

Note re advertising text:

The minimum order quantity corresponds to one pack unit quantity (VPE) or a multiple thereof.

Technical description

Glove size	7
Protection category	Category II
Type of glove	Cold protection gloves
Glove characteristics	Reinforced crook of the thumb
Glove characteristics	Hook & loop fastener
Contents	12
Application	reusable
Application range	All-round
Application range	Precision
Standard	EN 511
Length	230 mm
EN 388	2121X
EN 511	01X
Backing material	Full-grain goatskin leather, nylon
Coating variant	No coating
Colour	white / black
Type of product	Cold protection gloves