

Ansell**Pair of chemical protective gloves AlphaTec® 58-735, Glove size: 7****Order data**

Order number	094761 7
GTIN	10076490464490
Item class	04P

Description**Version:**

Alphatec® 58-735. The gloves provide an ideal combination of protection against many common chemicals with level C cut resistance. Good grip for handling oily or wet components. High comfort when wearing thanks to good freedom of movement for the fingers.

Category III safety gloves.

Note:

The minimum order quantity corresponds to one pack unit quantity (VPE) or a multiple thereof.
EN 374:2016: Type A (AJKLMNOPT)

Technical description

Glove size	7
Protection category	Category III
Type of glove	Chemicals protection gloves
Clothing standard	Oeko-Tex Standard 100
Contents	6

Glove characteristics	free of latex
Glove characteristics	Foodstuffs certified
Glove characteristics	Suitable for allergy sufferers
Glove characteristics	Silicone-free
Protection class	Protection against bacteriological risks according to EN 374
EN 374:2016	Type A (AJKLMNOPT)
Resistance to chemicals	AJKLMNOPT
EN 388:2016	4X32C
EN 407	X1XXXX
Material	Nitrile
Backing material	Nitril
AQL	0,65
Application range	All-round
Length	350 mm
Thickness	1 mm
Colour	black / green
Application	reusable
Weight	42 g
Cut protection class	C
Coating	Nitril
Coating variant	The palms of the hands
Type of product	Chemicals protection gloves