

**Burr Tooth profile INOX – coarse, Carbide, Type: A0616****Order data**

| | |
|--------------|---------------|
| Order number | 547250 A0616 |
| GTIN | 4045197973870 |
| Item class | 52D |

Description**Version:**

The innovative tooth geometry permits **very high metal removal rates** combined with **smooth cutting and good guidance accuracy**. Outstanding chip formation and surface results, low heat input into the material (no tempering colouration). Shank \varnothing 6mm.

Application:

Optimised for use on **austenitic, rust-resistant and acid-resistant steels**, soft titanium alloys and non-ferrous metals.

Technical description

| | |
|---------------------------|-------------------------------|
| Overall length | 50 mm |
| Shape description | cylindrical |
| Toothing grit designation | coarse |
| Head \varnothing | 6 mm |
| Shank \varnothing | 6 mm |
| Tooth type abbreviation | INOX |
| Head length | 18 mm |
| Series | STAINLESS STEEL tooth profile |
| Tool material | Carbide |
| Type of product | Burr |

User data

| | Suitability | V_c | ISO code |
|--------|---|----------------------|-----------------|
| Alu Mg | suitable only under restricted conditions | | |
| INOX | suitable | | |
| Ti | suitable only under restricted conditions | | |
| CuZn | suitable only under restricted conditions | | |