

**HOLEX****Burr Tooth profile INOX – coarse, Carbide, Type: A1225****Order data**

Order number	547250 A1225
GTIN	4045197973900
Item class	52D

**Description****Version:**

**The innovative tooth geometry** permits **very high metal removal rates** combined with **smooth cutting and good guidance accuracy**. Outstanding chip formation and surface results, low heat input into the material (no tempering colouration). Shank  $\varnothing$  6mm.

**Application:**

Optimised for use on **austenitic, rust-resistant and acid-resistant steels**, soft titanium alloys and non-ferrous metals.

**Technical description**

Head $\varnothing$	12.7 mm
Shank $\varnothing$	6 mm
Tooth type abbreviation	INOX
Shape description	cylindrical
Toothing grit designation	coarse
Overall length	70 mm
Head length	25 mm
Series	STAINLESS STEEL tooth profile
Tool material	Carbide
Type of product	Burr

**User data**

	<b>Suitability</b>	<b>V<sub>c</sub></b>	<b>ISO code</b>
Alu Mg	suitable only under restricted conditions		
INOX	suitable		
Ti	suitable only under restricted conditions		
CuZn	suitable only under restricted conditions		