



Two-leg extractor, Type: 5



Order data

Order number	880100 5
GTIN	4021176009846
Item class	83U

Description

Version:

With reversible extraction legs (**for external and internal extraction**). Extraction legs adjustable on cross beam for different workpiece \varnothing . Extraction legs and cross beam of high-quality tool steel; sturdy double-ended spindle (ball end and point end).

Application:

Universally applicable for extracting bearings, discs, gear wheels etc. On model 880100 size 5 the depth of reach can be extended from 400 mm (normal) up to 700 mm by adjusting the legs.

Technical description

External clamping range	105 - 750 mm
Power	15 t
Internal capacity	340 - 1000 mm
Depth of reach up to	700 mm
Number of hooks	2
External hexagon drive	41 mm

maximum torque	650 Nm
Weight	47 kg
Type of product	Two-leg extractor