

**Pair of gloves KX-10 OBSIDIAN, Glove size: 8****Order data**

Order number	094318 8
GTIN	6920790166677
Item class	02H

Description**Version:**

Close-fitting and light weight class 5 cut protection gloves with a mixture of polyurethane and nitrile coating for excellent grip.

- **Seamless backing material of HPPE with 18-gauge knitted technology.**
- **Reinforced thumb joint for increased working life.**
- **Stretch knitted cuffs.**

Note:

The minimum order quantity corresponds to one pack unit quantity (VPE) or a multiple thereof.

Technical description

Glove size	8
Type of glove	Cut-resistant gloves
Protection category	Category II
Contents	1
Washing	40 °C coloureds

Drying	air dry
Glove characteristics	Reinforced crook of the thumb
Glove characteristics	Suitable for allergy sufferers
Glove characteristics	DMF-free
Glove characteristics	Silicone-free
EN 388:2003	4542
EN 388:2016	4X42C
Backing material	HPPE
Coating	water-based PU/nitrile
Coating variant	The palms of the hands
Application range	All-round
Application range	Precision
Length	255 mm
Colour	black / brown
Knitted technology	18G
AQL	G-II 1.0 for critical, G-II 2.5 for major, G-II 4.0 for minor.
Application	reusable
Cut protection class	C
Type of product	Multi-purpose gloves