



Three-leg extractor, Type: 4



Order data

Order number	880130 4
GTIN	4021176005886
Item class	83U

Description

Version:

With reversible extraction legs (**for external and internal extraction**). Extraction legs adjustable on cross beam for different workpiece \varnothing . Extraction legs and cross beam of high-quality tool steel; sturdy double-ended spindle (ball end and point end).

Application:

Universally applicable for extracting bearings, discs, gear wheels etc. On model 880100 size 5 the depth of reach can be extended from 400 mm (normal) up to 700 mm by adjusting the legs.

Technical description

External clamping range	170 - 375 mm
Depth of reach up to	200 mm
Power	15 t
Internal capacity	200 - 500 mm
Number of hooks	3
External hexagon drive	36 mm

maximum torque	500 Nm
Weight	17.99 kg
Type of product	Three-leg extractor

Accessories

Pair of spare extractor legs Type / Clamping depth 3/200 mm	880200 3/200
Extended extractor legs (3 pieces) Type / Clamping depth 4/500 mm	880320 4/500
Spare extractor legs (3 pieces) Type / Clamping depth 3/200 mm	880220 3/200
Spare pressure spindle Type 4	880150 4
Hydraulic pressure spindle Type 1	880170 1