



Digital depth gauge IP 67 with data output, Measuring range: 300mm



Order data

Order number	418746 300
GTIN	2050001949707
Item class	46P

Description

Version:

Very large high-contrast LCD display. Character height 8 mm. With preset (dimension selection in advance). The caliper is resistant to water, emulsion, oil, and dust.

Function:

IP67: Protected against intermittent immersion in water and protected against penetration by dust (dust-tight), also completely protected against touching.

Supplied with:

Incl. battery No. 081560 size CR2032.

Optional extras:

Data cable No. 498948 size USB2. Measurement head.

Technical description

Calibration	A1
Scale divisions	0.0005 in
Article no of the battery / rechargeable battery fitted	081560 CR2032
Number of batteries contained	1
Measuring range	0 - 300 mm
Scale divisions	0.01 mm
Interface	RS232C interface
Interface	USB interface

Digit height LCD display	8 mm
Cross-section measuring beam	12×4 mm
Error limit	0.03 mm
Bridge length	100 mm
IP Index of Protection	IP 67
Power supply	Battery-powered
Standard	Manufacturer's standard
Reversible reading	mm / inch
Measurement technology	digital
Material	Stainless steel, INOX
all parts	hardened
Packaging	sturdy box
Type of product	Depth gauge

Services

DAkkS calibration Calipers / depth gauges maximum measuring range 300 mm	021010 300
Calibration Calipers / depth gauges maximum measuring range 300 mm	021000 300

Accessories

Connection cable Type USB2	498948 USB2
Button cell / special battery Battery type CR2032	081560 CR2032