

**Cordless drill / driver, Type: GSR1821****Order data**

Order number	070243 GSR1821
GTIN	3165140979412
Item class	03B

Description**Version:**

- **Compact, powerful cordless drill with forward/reverse operation.**
- **LED light to illuminate the working area and battery charge display.**
- **Multi-stage torque setting for precise screw driving.**
- **Electronic speed control for precise drilling and screw driving.**
- **Softgrip.**

Outstanding available and comfortable handling due to **compact design**. **Motor brake** for precise working.

Advantage:

Electronic Motor Protection.

Supplied with:

Supplied with 2× Li-ion batteries, charger and L-BOXX.

Note:

See from No. 073851 and No. 073863 – 073867 for suitable replacement batteries, starter sets and chargers.

Technical description

Speed range 2nd speed	0 - 1800 min ⁻¹
-----------------------	----------------------------

maximum twist drill size Ø in wood	35 mm
maximum vibration to EN	<2.5 m/s ²
maximum torque soft	21 Nm
Manufacturer's designation	GSR 18V-21
maximum torque hard	55 Nm
typical application	Medium
Packaging	Modular case (L-Boxx)
Battery capacity	2 Ah
Motor design	4-pole DC motor
maximum twist drill size Ø in steel	13 mm
Quick-clamping chuck range	1.5 - 13 mm
Weight	1.7 kg
suitable battery - supplier / battery type / voltage	Bosch 18 V
Speed range 1st speed	0 - 480 min ⁻¹
Battery voltage	18 V
Number of rechargeable batteries contained	2
Type of rechargeable battery	Lithium-ion
Power supply	Rechargeable battery-powered
Suitable for material	Steel
Suitable for material	wood
Type of product	Drill/driver
USP1	18V, 4-pole DC motor
USP2	Quick-change chuck clamping range 1.5-13, with 2 batteries, in L-Boxx

Accessories

Battery charger Type 1880CV	073866 1880CV
Wireless charging starter set Type GAL1830W	073862 GAL1830W

Li-ion battery Battery type, battery voltage B18 V

073851 B18