

**FlexiClick system cordless drill / driver, Type: GSR1860FC****Order data**

Order number	070107 GSR1860FC
GTIN	3165140906067
Item class	03B

**Description****Version:**

Cordless drill/driver

- **Compact, powerful cordless drill with forward/reverse operation.**
- **With Electronic Motor Protection (EMP) and Electronic Cell Protection (ECP).**
- **LED light to illuminate the working area and battery charge display.**
- **Multi-stage torque setting for precise screw driving.**
- **Electronic speed control for precise drilling and screw driving.**
- **Softgrip.**

Can be retrofitted with a **connectivity** module. Maximum flexibility and precise work even at inaccessible places, thanks to exchangeable **eccentric or angled options**. Hammer drilling in concrete with 1 Joule impact energy, thanks to the **SDS-Plus hammer option**. **Head length including bit holder only 147 mm.**

**Supplied with:**

Supplied with 2× 5.0 Ah Li-ion batteries, charger, carrying case, additional handle. With many adjustable options within the FlexiClick system: Drill chuck, angle option, eccentric option, SDS-Plus hammer option.

**Note:**

See No. 073851 ff. and 073866 ff for suitable spare batteries, starter sets and chargers.

Packaging: Modular case (L-Boxx)

suitable battery - supplier / battery type / voltage: Bosch 18 V

Manufacturer's designation: GSR 18V-60FC set

Motor design: Brushless motor

Battery capacity: 5 A·h

Battery voltage: 18 V

maximum torque soft: 31 N·m

maximum torque hard: 60 N·m

## Technical description

Battery voltage	18 V
Speed range 1st speed	0 - 600 rpm
suitable battery - supplier / battery type / voltage	Bosch 18 V
maximum vibration to EN	<2.5 m/s <sup>2</sup>
Speed range 2nd speed	0 - 1900 rpm
Quick-clamping chuck range	1.5 - 13 mm
Motor design	Brushless motor
maximum twist drill size Ø in wood	38 mm
Packaging	Modular case (L-Boxx)
maximum torque soft	31 N·m
Weight	1.7 kg
maximum torque hard	60 N·m
Manufacturer's designation	GSR 18V-60FC set
Battery capacity	5 A·h
maximum twist drill size Ø in steel	13 mm
typical application	Strong

## Accessories

Battery charger Type 1880CV	073866 1880CV
Li-ion battery Battery type, battery voltage B18 V	073854 B18
Wireless charging starter set Type GAL1830W	073862 GAL1830W