



Cordless drill / driver, Type: M12FDD4



Order data

Order number	070210 M12FDD4
GTIN	4058546029906
Item class	03L

Description

Version:

MILWAUKEE – Cordless power drill

Powerful cordless 2-speed drill / driver, reversible. REDLITHIUM™ rechargeable batteries with **single-cell monitoring** and **charge status display**.

Sturdy **metal gearbox** for long working life.

FIXTEC metal quick-clamping drill chuck with spindle lock.

LED illumination of the working area. Handle with Softgrip coating for comfortable use.

- **Brushless POWERSTATE™ motor for more power and a compact shape (168 mm in length).**
- **REDLINK PLUS™ electronics for intelligent power management and overload protection.**
- **16-step electronic torque limit setting, plus drill steps.**

Advantage:

REDLINK PLUS™ electronics.

Supplied with:

Supplied with 2x 12 V / 4.0 Ah Li-ion batteries, charger, belt clip, HD box.

Note:

See from No. 073815 and No. 073840 for suitable replacement batteries and chargers.

Packaging: Modular case (HD=Heavy Duty)

suitable battery - supplier / battery type / voltage: Milwaukee type B 12 V

Manufacturer's designation: M12FDD-402X

Motor design: Brushless motor
 Number of rechargeable batteries contained: 2
 Type of rechargeable battery: Lithium-ion
 Battery capacity: 4 A·h
 Battery voltage: 12 V

Technical description

maximum speed 1st speed	0 - 450 min ⁻¹
maximum twist drill size Ø in wood	35 mm
typical application	Strong
Motor design	Brushless motor
Manufacturer's designation	M12FDD-402X
maximum twist drill size Ø in steel	13 mm
maximum vibration to EN	< 2.5 m/s ²
Quick-clamping chuck range	1.5 - 13 mm
Battery voltage	12 V
maximum torque hard	44 N·m
Weight	1.5 kg
suitable battery - supplier / battery type / voltage	Milwaukee type B 12 V
Packaging	Modular case (HD=Heavy Duty)
maximum speed 2nd speed	1700 min ⁻¹
Battery capacity	4 A·h
Number of rechargeable batteries contained	2
Type of rechargeable battery	Lithium-ion
Power supply	Rechargeable battery-powered
Suitable for material	wood
Suitable for material	Steel
Type of product	Drill/driver

Accessories

Offset screwdriving attachment Type WB1	073920 WB1
Battery charger Type M1218FC	073840 M1218FC
Battery charger Type M1218C	073840 M1218C
Offset screwdriving attachment Type OSD2	073920 OSD2
Li-ion system M12B4 Rechargeable battery type, battery voltage MB12 V	073815 MB12