

# AEG

## Cordless drill / driver, Type: BS18C2X



### Order data

Order number	070222 BS18C2X
GTIN	4058546010843
Item class	07A

### Description

#### Version:

#### AEG – Cordless drill / driver

- Sturdy and handy cordless 2-speed drill / screwdriver, reversible.
- FIXTEC quick-change chuck with spindle lock.
- Handle with Softgrip coating for comfortable use.
- LED illumination of the working area.
- 23-step torque limit adjustment, plus drill steps.
- 13 mm quick-change chuck.
- 4-pole motor for maximum power within a compact design.

#### Version of the advertising text:

- Sturdy and handy cordless 2-speed drill / driver, reversible.
- FIXTEC quick-change chuck with spindle lock.
- Handle with Softgrip coating for comfortable use.
- 23-step torque limit adjustment, plus drill steps.
- 13 mm quick-change chuck.

#### Advantage:

23-step torque adjustment.

#### Supplied with:

Supplied with 2 × 2.0 Ah batteries, charger, transport case.

**Attention:**

German version. Order free UK adapter plug No. 08 1172\_GB.

**Note:**

See No. 073820 and No. 073846 – No. 073848 for suitable replacement batteries and chargers. Suitable chargers and starter sets can be found under No. 073841 and No 073844.

## Technical description

Battery capacity	2 Ah
maximum twist drill size Ø in wood	45 mm
Weight	1.7 kg
maximum twist drill size Ø in steel	13 mm
Battery voltage	18 V
Packaging	Carrying case
typical application	Strong
maximum vibration to EN	< 2.5 m/s <sup>2</sup>
Manufacturer's designation	BS 18 C2X
maximum speed 1st speed	0 - 450 min <sup>-1</sup>
Quick-clamping chuck range	1.5 - 13 mm
maximum speed 2nd speed	1800 min <sup>-1</sup>
maximum torque hard	50 Nm
Motor design	4-pole motor
suitable battery - supplier / battery type / voltage	AEG type B 18 V
Number of rechargeable batteries contained	2
Type of rechargeable battery	Lithium-ion
Power supply	Rechargeable battery-powered
Suitable for material	wood
Suitable for material	Steel
Type of product	Drill/driver
USP1	18V
USP2	FIXTEC quick-change chuck, with softgrip

---

## Accessories

Offset screwdriving attachment Type OSD2	073920 OSD2
Battery charger Type BL1418	073841 BL1418
Offset screwdriving attachment Type WB1	073920 WB1