



Three-leg extractor, Type: 10



Order data

Order number	880130 10
GTIN	4021176013621
Item class	83U

Description

Version:

With reversible extraction legs (**for external and internal extraction**). Extraction legs adjustable on cross beam for different workpiece \varnothing . Extraction legs and cross beam of high-quality tool steel; sturdy double-ended spindle (ball end and point end).

Application:

Universally applicable for extracting bearings, discs, gear wheels etc. On model 880100 size 5 the depth of reach can be extended from 400 mm (normal) up to 700 mm by adjusting the legs.

Technical description

Power	6 t
Internal capacity	70 - 180 mm
External clamping range	27 - 130 mm
Depth of reach up to	100 mm
Number of hooks	3
maximum torque	80 Nm

External hexagon drive	17 mm
Weight	1.59 kg
Type of product	Three-leg extractor

Accessories

Pair of spare extractor legs Type / Clamping depth 1/100 mm	880200 1/100
Extended extractor legs (3 pieces) Type / Clamping depth 1/200 mm	880320 1/200
Spare extractor legs (3 pieces) Type / Clamping depth 1/100 mm	880220 1/100
Spare pressure spindle Type 1	880150 1