



Two-leg extractor, Type: 1



Order data

Order number	880100 1
GTIN	4021176009433
Item class	83U

Description

Version:

With reversible extraction legs (**for external and internal extraction**). Extraction legs adjustable on cross beam for different workpiece \varnothing . Extraction legs and cross beam of high-quality tool steel; sturdy double-ended spindle (ball end and point end).

Application:

Universally applicable for extracting bearings, discs, gear wheels etc. On model 880100 size 5 the depth of reach can be extended from 400 mm (normal) up to 700 mm by adjusting the legs.

Technical description

Depth of reach up to	100 mm
Internal capacity	70 - 140 mm
External clamping range	30 - 90 mm
Power	4.5 t
Number of hooks	2
maximum torque	80 Nm

External hexagon drive	17 mm
Weight	1.305 kg
Type of product	Two-leg extractor

Accessories

Spare pressure spindle Type 1	880150 1
Spare extractor legs (3 pieces) Type / Clamping depth 1/100 mm	880220 1/100
Pair of spare extractor legs Type / Clamping depth 1/100 mm	880200 1/100
Pair of extended extractor legs Type / Clamping depth 1/200 mm	880300 1/200