



Three-leg extractor, Type: 2



Order data

Order number	880130 2
GTIN	4021176013478
Item class	83U

Description

Version:

With reversible extraction legs (**for external and internal extraction**). Extraction legs adjustable on cross beam for different workpiece \varnothing . Extraction legs and cross beam of high-quality tool steel; sturdy double-ended spindle (ball end and point end).

Application:

Universally applicable for extracting bearings, discs, gear wheels etc. On model 880100 size 5 the depth of reach can be extended from 400 mm (normal) up to 700 mm by adjusting the legs.

Technical description

Power	7 t
Depth of reach up to	150 mm
External clamping range	35 - 160 mm
Internal capacity	100 - 220 mm
Number of hooks	3
maximum torque	150 Nm

External hexagon drive	22 mm
Weight	3.815 kg
Type of product	Three-leg extractor

Accessories

Spare pressure spindle Type 2	880150 2
Pair of spare extractor legs Type / Clamping depth 2/150 mm	880200 2/150
Spare extractor legs (3 pieces) Type / Clamping depth 2/150 mm	880220 2/150
Extended extractor legs (3 pieces) Type / Clamping depth 2/300 mm	880320 2/300