



## Two-leg extractor, Type: 10



### Order data

Order number	880100 10
GTIN	4021176009921
Item class	83U

### Description

#### Version:

With reversible extraction legs (**for external and internal extraction**). Extraction legs adjustable on cross beam for different workpiece  $\varnothing$ . Extraction legs and cross beam of high-quality tool steel; sturdy double-ended spindle (ball end and point end).

#### Application:

Universally applicable for extracting bearings, discs, gear wheels etc. On model 880100 size 5 the depth of reach can be extended from 400 mm (normal) up to 700 mm by adjusting the legs.

### Technical description

Power	4.5 t
Internal capacity	70 - 180 mm
External clamping range	30 - 120 mm
Depth of reach up to	100 mm
External hexagon drive	17 mm
maximum torque	80 Nm

Number of hooks	2
Weight	1.42 kg
Type of product	Two-leg extractor

---

## Accessories

Pair of spare extractor legs Type / Clamping depth 1/100 mm	880200 1/100
Spare extractor legs (3 pieces) Type / Clamping depth 1/100 mm	880220 1/100
Pair of extended extractor legs Type / Clamping depth 1/200 mm	880300 1/200
Spare pressure spindle Type 1	880150 1