

**VHB™ Power adhesive tape, Manufacturer's designation: 4991F****Order data**

Order number	083785 4991F
GTIN	4054596308541
Item class	08M

Description**Version:**

Double-sided high-performance **adhesive tape** of pure acrylate adhesive (VHB) for permanently strong bonds. High instant tack, high resistance to temperature, weather, UV and solvents. Excellent sealing function, vibration-damping. Very strong bonding on virtually all materials, for universal applications.

Application:

Suitable for metals, painted surfaces, painted wood, glass, ceramics and many plastics. For use indoors and outdoors.

Length: 5.5 m

Width: 19 mm

Colour: grey

Short-term temperature-resistant to: 150 °C

Long-term temperature-resistant to: 90 °C

Technical description

Thickness	2.3 mm
Width	19 mm
Manufacturer's designation	4991F

Colour	grey
Length	5.5 m
Material of covering	Siliconised PE film
Stretch capability	300 %
Backing material	PE
Application	Sealing
Application	Attaching
Application	Masking
Application	Indoor and outdoor areas
Adhesive strength on steel	4.5 N/mm
Storage humidity	50 - 60 %
Storage temperature	20 - 23 °C
temperature-resistant up to	90 - 150 °C
Type of adhesive tape	double-sided
Number of adhesive tapes	1
Adhesive	Acrylate
Special features	damping
Special features	clings well
Special features	moisture-resistant
"Best before" date	12 month