



## VHB™ Power adhesive tape, Manufacturer's designation: 5962F



### Order data

Order number	083785 5962F
GTIN	4054596308619
Item class	08M

### Description

#### Version:

**Double-sided** high-performance **adhesive tape** of pure acrylate adhesive (VHB) for permanently strong bonds. High instant tack, high resistance to temperature, weather, UV and solvents. Excellent sealing function, vibration-damping. Ideally suited to bonding to many low-energy surfaces, powder-coated surfaces, plastics or glass.

#### Application:

Suitable for metals, painted surfaces, painted wood, glass, ceramics and many plastics. For use indoors and outdoors.

Length: 8 m

Width: 19 mm

Colour: black

Short-term temperature-resistant to: 150 °C

Long-term temperature-resistant to: 90 °C

### Technical description

Manufacturer's designation	5962F
Length	8 m
Thickness	1.6 mm

Colour	grey
Width	19 mm
Material of covering	Siliconised PE film
Backing material	PE
"Best before" date	12 month
Number of adhesive tapes	1
Type of adhesive tape	double-sided
Adhesive strength on steel	5.5 N/mm
Adhesive	Acrylate
Storage temperature	20 - 23 °C
Storage humidity	50 - 60 %
temperature-resistant up to	120 - 150 °C
Special features	damping
Special features	clings well
Application	Sealing
Application	Masking
Application	Attaching
Stretch capability	300 %