

**Ansell**
**Pair of gloves ActivArmr Hycron® 27-607, Glove size: 10**

**Order data**

Order number	094430 10
GTIN	10076490498808
Item class	04P

**Description**
**Version:**

ActivArmr Hycron® series. **Hard-wearing gloves** of jersey cotton with nitrile coating for the most demanding applications. High resistance to sharp-edged and chafing materials. Robust and more flexible than PVC, three times longer service life than heavy leather gloves. **Effective barrier against greases and oils.** Particularly suitable for rough castings, moulded plastic parts, steel bar, sheet metal, high-tensile cable, building materials, unfinished wood. With knitted cuffs and 3/4 coating for maintaining better breathability.

**Standard:**

EN 388; EN ISO 21420

Antistatisch gemäß EN 1149.

**Note:**

The minimum order quantity corresponds to one pack unit quantity (VPE) or a multiple thereof.

**Technical description**

Accuracy of fit	good
Glove size	10
Wet grip	good

Oil grip	good
Breathability	medium
Heat protection	not available
silicone-free	yes
Touch sensitivity	medium
DMF-free	no
Material of coating	Nitrile
Series	Hycron®
Protection category	Category II
Type of glove	Multi-purpose gloves
Contents	12
Glove characteristics	Silicone-free
Glove characteristics	free of latex
EN 388	4221X
Backing material	Cotton
Coating	Nitril
Coating variant	3/4 coating
Application range	Heavy Duty
Length	246 mm
Colour	blue
Weight	57 g
Application	reusable
Material	Nitrile
Type of product	Multi-purpose gloves