



Two-leg extractor, Type: 2



Order data

Order number	880100 2
GTIN	4021176009501
Item class	83U

Description

Version:

With reversible extraction legs (**for external and internal extraction**). Extraction legs adjustable on cross beam for different workpiece \varnothing . Extraction legs and cross beam of high-quality tool steel; sturdy double-ended spindle (ball end and point end).

Application:

Universally applicable for extracting bearings, discs, gear wheels etc. On model 880100 size 5 the depth of reach can be extended from 400 mm (normal) up to 700 mm by adjusting the legs.

Technical description

Depth of reach up to	150 mm
Power	6 t
External clamping range	40 - 160 mm
Internal capacity	100 - 220 mm
maximum torque	150 Nm
External hexagon drive	22 mm

Number of hooks	2
Weight	3.01 kg
Type of product	Two-leg extractor

Accessories

Spare pressure spindle Type 2	880150 2
Pair of spare extractor legs Type / Clamping depth 2/150 mm	880200 2/150
Spare extractor legs (3 pieces) Type / Clamping depth 2/150 mm	880220 2/150
Pair of extended extractor legs Type / Clamping depth 2/300 mm	880300 2/300